

## LCN Installation Instructions/Templates Index

### 1250 Series

Mounting/Document	Template Number
Pull, Top Jamb, PA mounts	<a href="#">71375</a>
EDA and HEDA	<a href="#">71378</a>
CUSH and Spring CUSH mounts	<a href="#">71379</a>
Drop plate	<a href="#">71930</a>
419 flush adapter	<a href="#">72012</a>

### 1260 Series

Mounting/Document	Template Number
Pull, Top Jamb mounts	<a href="#">29804</a>
PA mount	<a href="#">29805</a>
EDA mount	<a href="#">29808</a>
CUSH and Spring CUSH mounts	<a href="#">29809</a>
Drop plate	<a href="#">29810</a>
Quick fix	<a href="#">29811</a>
62A Shoe	<a href="#">29901</a>

### 1450 Series

Mounting/Document	Template Number
Pull, Top Jamb, PA mounts	<a href="#">71928</a>
EDA and HEDA mounts	<a href="#">71931</a>
CUSH and Spring CUSH mounts	<a href="#">71932</a>
Drop plate	<a href="#">71376</a>
419 flush adapter	<a href="#">72012</a>

### 1450T Series

Mounting/Document	Template Number
Track mounts	<a href="#">72042</a>
Drop plate	<a href="#">72043</a>

### 1460 Series

Mounting/Document	Template Number
Pull, Top Jamb mounts	<a href="#">28011</a>
PA mount	<a href="#">28012</a>
EDA mount	<a href="#">28013</a>
CUSH and Spring CUSH mounts	<a href="#">28014</a>
Drop Plate	<a href="#">28460</a>
Designer Series cover	<a href="#">28090</a>

### 1460T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28020</a>
Drop Plate	<a href="#">28460</a>
Designer Series cover	<a href="#">28090</a>

### 2010 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">18755</a>

### 2030 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">18758</a>

### 2210 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">27297</a>
2210DPS Series	<a href="#">18363</a>

### 2310ME Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">19911</a>
2310ME-420	<a href="#">18766</a>

### 2610 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">19963</a>

### 2800 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">740132</a>
Control box	<a href="#">740100</a>
Control box retrofit	<a href="#">740130</a>
Offset pivot arm	<a href="#">740013</a>

### 3030 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">19623</a>

### 3130 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">25051</a>

### 3130SE Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">18781</a>

### 4000T Series

Mounting/Document	Template Number
Track mounts	<a href="#">19580</a>

### 4010 Series

Mounting/Document	Template Number
Track mounts	<a href="#">28476</a>
Regular arm mounts	<a href="#">28475</a>
Drop plate	<a href="#">28499</a>
Fusible link	<a href="#">26367</a>

### 4010T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28476</a>
Track DE mounts	<a href="#">23652</a>
Drop plate	<a href="#">28499</a>

### 4020 Series

Mounting/Document	Template Number
Regular arm mounts	<a href="#">28477</a>
Drop plate	<a href="#">28500</a>
Fusible link	<a href="#">26367</a>

### 4020T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28478</a>
Drop plate	<a href="#">28500</a>

### 4030 Series

Mounting/Document	Template Number
Pull and PA side mounts	<a href="#">28987</a>
Top Jamb push side mount	<a href="#">28988</a>
EDA mount	<a href="#">28989</a>
CUSH arm/Spring CUSH mounts	<a href="#">28990</a>
Drop plate	<a href="#">26125</a>

### 4030T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28991</a>
Drop plate	<a href="#">26125</a>

### 4040XP Series

Mounting/Document	Template Number
Pull, Top Jamb, PA mounts	<a href="#">73182</a>
EDA mount	<a href="#">28267</a>
CUSH arm/Spring CUSH mounts	<a href="#">28266</a>
Drop plate	<a href="#">28466</a>

### 4040T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28268</a>
Drop plate	<a href="#">28466</a>

### 4040SE Series

Mounting/Document	Template Number
404SE mount	<a href="#">24213</a>
4040SEC mount	<a href="#">24213</a>
4040SEL mount	<a href="#">24191</a>
404SE Double Egress mount	<a href="#">24771</a>

### 4050A Series

Mounting/Document	Template Number
Pull, Top Jamb, PA mounts	<a href="#">73089</a>
EDA and HEDA mounts	<a href="#">73091</a>

Mounting/Document	Template Number
CUSH and Spring CUSH mounts	<a href="#">73092</a>
Drop plate	<a href="#">73094</a>
62A Shoe	<a href="#">73093</a>
Mounting information sheet	<a href="#">73132</a>

### 4050A T Series

Mounting/Document	Template Number
Track mounts	<a href="#">73128</a>

### 4110 Series

Mounting/Document	Template Number
Regular arm mounts	<a href="#">28479</a>
CUSH and Spring CUSH mounts	<a href="#">28481</a>
Drop plate	<a href="#">28501</a>
Fusible link	<a href="#">26367</a>

### 4110T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28480</a>
Drop plate	<a href="#">28501</a>

### 4210 Series

Mounting/Document	Template Number
Regular arm mounts	<a href="#">28482</a>
CUSH mount	<a href="#">28483</a>
Drop plate	<a href="#">28501</a>

### 4210T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28484</a>
Drop plate	<a href="#">28501</a>

### 4310ME Series

Mounting/Document	Template Number
4310ME	<a href="#">18762</a>
4310ME DE	<a href="#">18789</a>

### 4310HSA Series

Mounting/Document	Template Number
4311HSA	<a href="#">25073</a>

### 4410ME Series

Mounting/Document	Template Number
4410ME	<a href="#">15022</a>
4410MEC	<a href="#">24826</a>

### 4510 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">28485</a>
Drop plate	<a href="#">28499</a>

### 4510T Series

Mounting/Document	Template Number
Track mounts	<a href="#">28486</a>
Drop plate	<a href="#">28499</a>

### 4630/4640 Series

Mounting/Document	Template Number
4630/4640 Series instruction booklet	<a href="#">28101</a>
4630CS/4640CS Series instruction booklet	<a href="#">29268</a>
334 concealed switch retrofit	<a href="#">29293</a>
7910-219 remote key switch	<a href="#">29285</a>

### 4810 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">24827</a>

### 4820 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">24828</a>

### 4840 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">25381</a>

### 5010 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">13187</a>

### 5030 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">14126</a>

### 6030 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">18503</a>

### 7900 Series

Mounting/Document	Template Number
7901 and ES7901 models	<a href="#">23760</a>
7902 and ES7902 models	<a href="#">23761</a>
7902SEQ and ES7902SEQ control box	<a href="#">23762</a>
7800 Compressor service kit	<a href="#">26941</a>
7981 and ES7981 models	<a href="#">23665</a>
7982 model	<a href="#">23654</a>
7982SEQ model	<a href="#">23657</a>
ES7982 control box	<a href="#">23655</a>
ES7982SEQ model	<a href="#">23656</a>
Filter service kit 980 and 7980	<a href="#">25848</a>
7949 and ES7949 models	<a href="#">19282</a>
3210 24VAC transformer	<a href="#">27032</a>

### 8310 Series

Mounting/Document	Template Number
8310 full length actuator user guide	<a href="#">109467</a>
8310 full length actuator template	<a href="#">110626</a>

### 9130 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">740158</a>

### 9140 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">740158</a>

### 9150 Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">740158</a>

### 9500 Series

Mounting/Document	Template Number
9500 Series installation instructions	<a href="#">740132</a>
Control box installation instructions	<a href="#">740100</a>
Control box retrofit instructions	<a href="#">740130</a>
Offset pivot arm	<a href="#">740013</a>
Pull arm mount	<a href="#">740009</a>
Push arm mount	<a href="#">740008</a>

### SEH Series

Mounting/Document	Template Number
All mounts/installation instructions	<a href="#">19842</a>

### SEM 1900 Series

Mounting/Document	Template Number
SEM1960	<a href="#">29426</a>
SEM1970/1980	<a href="#">29429</a>

### SEM 7800 Series

Mounting/Document	Template Number
SEM7810	<a href="#">29359</a>
SEM7820	<a href="#">29350</a>
SEM7830	<a href="#">29351</a>
SEM7840/7850	<a href="#">29352</a>

### Additional documents

Mounting/Document	Template Number
Optional bumper installation instructions	<a href="#">72694</a>